

FES / Dunham - Bush Screw Compressor Package – 200 HP

Mfg: FES / Dunham - Bush

Model: 550B / 2516

Stock No: JSKS01

Serial No: 79-0180-0305

FES / Dunham - Bush Screw Compressor Package. Model: 550B / 2516. S/N: 79-0180-0305. FES contract number: 79-0180-0305-09. Capacity rating: 217 tons at 192 BHP using R-717(ammonia). Dunham - Bush compressor, model: 550-BX, no. 3031. Leak test pressure 313 psig, Hyd. test pressure 470. Displacement 1668 cfm. Reliance Electric Industrial Co. motor, Duty Master®: model: P44G4400B, ID no. 01MN444400G001AA, 200 hp, 3750 rpm, 460V, amps: 220, frame size: 4441s, design: B continuous duty drip proof enclosure, 3 phase, 60 Hz. Oil separator: FES no. 79156. National Board no: 803, MAWP: 250 psi, MDMT 300 psi, MAWT: -20F, HD RAD 2:1, HD TK.375, SHL TK.375. Equipped with FES control panel, oil pump and De Laval Barksdale temperature switch number ML1H-H204-WS. Media temperature limits: from -100F to 250F. Hours on compressor: 36,290. Overall dimensions: 12 ft. 7-3/4 in. L x 5 ft. W x 8 ft. 7 in. H.









