



- NOTES:**
1. (A) - FAN MOTOR LOCATION
 2. MAKE-UP WATER PRESSURE 20 ps1 MIN. 50 ps1 MAX.
 3. 3/4" DIA. MOUNTING HOLES, REFER TO RECOMMENDED STEEL SUPPORT DNG. NO. SP1821
 4. H - APPROXIMATE DIMENSION, DO NOT USE FOR PREFABRICATION OF CONNECTING PIPING
 5. MAKE-UP CONNECTION LOCATED 7'-1/2" FROM CONNECTION

REVISION No. 3

MODEL	WEIGHTS			DIMENSIONS		
	SHIPPING	OPER.	HEAVIEST SECTION	H	C	R
LSHA 20AA2	2250	3310	2250	6'-8-1/2"	3'-1-1/8"	12"
LSHA 20A2	2670	3840	1680	7'-4"	3'-8-5/8"	19-1/2"
LSHA 20B2	3030	4310	2040	7'-11-1/2"	4'-4-1/8"	27"
LSHA 20C2	3470	4870	2430	8'-7"	4'-11-5/8"	34-1/2"

DOUBL-KOLD

CERTIFIED FOR: _____ EVAPCO NO: #96-9088W

CUSTOMERS ORDER NO: #96001734

CAPACITY: 40 GPM

FAN MOTOR *1) 5 HP H.P. ELEC. SPEC. 460/3/60 TERC 0" ESP

PUMP MOTOR 1) 3/4 HP H.P. ELEC. SPEC. 460/3/60 TERC

REMARKS Accessories: *Fan Motor = 2 Speed, 1 Winding, Series Flow Pressure Drop Through Coils = .4 psi



closed circuit cooler

REV: