

Horizontal Feeder Auger Conveyors

Mfg:

Model:

Stock No: MRSP116

Serial No:

Horizontal Feeder Auger Conveyors. Approximately 7 ft. long w/ motors and drives. Double auger conveyor system, (1) 1 ft. 3 ½ in. diameter common centered infeed. Conveys in 2 directions. (2) trough approximate dimensions: 7 ft. L x 10 in. W x 1 ft. deep. (2) Baldor Electric motors, 1 ½ hp, 1140 rpm, 230/460 V, 5/2.5 amps, 60 hz, 3 phase. (2) Falk enclosed gear drives, ratio: 14.43: 1. Final rpm: 79. Inlet: (1) 1 ft. 3 ½ in. dia. port. Outlets: (1) 10 in. W x (1) 1 ft. 7 in. H, (1) 10 in. W x 1 ft. 8 in. H. Overall dimensions: 9 ft. 8 in. L x 3 ft. W x 4 ft. 8 in. H.(BH).







