

**1990 Universal International, Inc. / Universal Industries Vertical Bucket Elevator**

**Mfg: Universal International, Inc. / Universal Industries**

**Model: U1-630**

**Stock No: MRSP125**

**Serial No: 59705**

1990 Universal International, Inc. / Universal Industries Vertical Bucket Elevator. Model: U1-630. S.O: 59705. Capacity of free flowing material @ 75% Bucket fill: 630 ft<sup>3</sup>/h. Bucket spacing: 4 ½ in. Buckets size: 6 in. x 4 in. Belt Speed: 270 fpm. Belt width: 6 ½ in. Baldor Electric motor, 1-½ hp, 1740 rpm, 230/460 V, 4.2/2.1 amps, 60 Hz, 3 phase. Dodge torque arm speed reducer, ratio: 25.54. Final rpm: 68. U1 series bucket elevators applications include hot, abrasive, heavy, corrosive, hygroscopic and wet materials, and also features an exclusive "easy dump" design. Inlet: (1) 8 in. W x 1 ft. 1 ½ in. H port, (1) 7 ½ in. W x 11 ½ in. H port. (1) 3-½ in. side access port. Outlets: (1) 8 in. W x 9 in. H port. Overall dimensions: 4 ft. 9 in. L x 1 ft. W x 18 ft. 9 in. H.(BH)(ACN55).



