

2001 Cornell Centrifugal Pump

Mfg: Cornell

Model: 1.5CBH-5-3-4

Stock No: KWBF209.8a

Serial No: 119250

2001 Cornell Centrifugal Pump. Model: 1.5CBH-5-3-4. S/N: 119250. Flow rate for new pump is 32 gpm with required horsepower and pressure. Discuss with salesperson your process to determine if this refurbished pump should handle your specific duty. Impeller diameter: 11 in. John Crane, 1.25", T-1, double mechanical shaft seal with pressurized barrier fluid lubrication system, low oil limit switch, and seal chamber heater to maintain proper barrier oil viscosity. Baldor industrial motor, 5 hp, 1750 rpm, 230/460 V, 13.4/5.7 amps, 60 Hz, 3 phase. Inlets: (1) 3-1/2 in. dia. Flanged port. Outlets: (1) 1-1/2 in. dia. Flanged port. Overall dimensions: 2 ft. 2 in. L x 1 ft. 7 in. W x 1 ft. 3 in. H. (ACN72).





