

2001 Krauss Maffei Screw Motor & Gearing

Mfg: Krauss Maffei

Model:

Stock No: MYDM407

Serial No:

2001 Krauss Maffei Screw Motor & Gearing. Typ: FZ251.3-V-FQD16, GETRIEBE-KM-NR. Oswald electric motor: 3350 rpm, 138 amps, 350 V, 115 Hz. Cooling: Flow-rate 9L/min. 1 bar max. 8 bar max. 25°C / 77°F. Overall dimensions: 3 ft. 8 in. L x 2 ft. 3 in. W. x 1 ft. 1 in. H.







OSWALD ELEKTROMOTOREN GmbH		AC Motor		CE
D - 63897 MILTENBERG / MAIN				
FQD16.3W-IEC - SoG - 65		Part No.	0967-000024	
Ser.No.	124121 - 2001	Cust. No.	6439816	
P_n	65 kW	$U_N \Delta/Y$	/ 350 V	
Poles	4 $\cos \psi_n$ 0.83	$I_n \Delta/Y$	/ 138 A	
n_n/n_{max}	2055 / 3350 rpm	f_n / f_{max}	70 / 115 Hz	
Ins. Cl.	F	Vib. Cl.	R	Balance H m 250 kg
Rating	S 3 - 60 % ED	Enclosure IP	54	
Tacho / Encoder	Brake			
Type	ROD420 - 2500 IU	Nm		
U_t	5 V - TTL	U_b	V_{oc}	V_{AC}
Cooling				
Durchsatz 9 l/min. 1 bar max. 8 bar max. 25°C				
Made in Germany www.oswald.de EN 60034				

Knödler		K. & A. Knödler GmbH 73760 Ostfildern	
Typ	7251.3-VE-FQD16	Nr.	54367
n_1	2055 min ⁻¹	P	65 kW
n_2	130 min ⁻¹	i	10.52
M_2	Nm	Baujahr	2001
Knödler		K. & A. Knödler GmbH 73760 Ostfildern	
Typ	6440279-KM-NR	Nr.	6440279
n_1	min ⁻¹	P	kW
n_2	min ⁻¹	i	8272013
M_2	Nm	Baujahr	

Knödler		K. & A. Knödler GmbH 73760 Ostfildern	
Typ	7251.3-VE-FQD16	Nr.	54367
n_1	2055 min ⁻¹	P	65 kW
n_2	130 min ⁻¹	i	10.52
M_2	Nm	Baujahr	2001
Knödler		K. & A. Knödler GmbH 73760 Ostfildern	
Typ	6440279-KM-NR	Nr.	6440279
n_1	min ⁻¹	P	kW
n_2	min ⁻¹	i	8272013
M_2	Nm	Baujahr	