

Evapco 3-Fan Evaporator – 42.1 Tons

Mfg: Evapco

Model: TFC3-8184-150P

Stock No: KWBF508

Serial No: 971283

1997 Evapco 3-Fan Evaporator. Model: TFC3-8184-150P. S/N: 971283. Refrigerant: R-717 (Ammonia). Nominal capacity: 42.1 tons. Fins per inch: 4. Coil rows: 8. Tube diameter: 1 in. Design pressure: 250 psi. Tube and fin material of construction: galvanized steel. Number of fans: 3. Fan diameter: 3 ft. 6 in. (3) Toshiba high efficiency motors, 1.5 hp , 1160 rpm, 230/460V. Unit has hot gas defrost coil only and is designed for 35°F room temperature. Inlets/outlets: (2) 1-1/2 in. dia. port. (1) 3 in. dia. port. Overall dimensions: 18 ft. 2-5/8 in. L x 4 ft. 5 in. W x 6 ft. 7 in. H.(ACN262)(BK).







evapco

EVAPCO, INC.
 5151 Allendale Lane Taneytown, MD 21787
 (410) 756-2600 Fax (410) 756-6450
 U.S. PATENT NO. 5,425,414 MADE IN U.S.A.

EVAPORATOR MODEL NUMBER TFC3-8184-150F	SERIAL NUMBER 971283
BELT NUMBER	DESIGN PRESSURE 250 P.S.I.G.

FOR EVAPCO AUTHORIZED PARTS AND SERVICE, CONTACT MR. GOODTOWER™

Mr. Goodtower
FRED SELL & ASSOCIATES
 2145 N.W. Military Highway, Suite 100
 San Antonio, TX 78213
 Phone (512) 330-0270

HIGH EFFICIENCY WORLD ENERGY

3-PHASE INDUCTION MOTOR

MODEL NO. **010-00199F** ENCL. **1**

TYPE	VOLTS	Hz
FORM	RPM	
FR.#	AMP.	
DUTY	SER. NO.	
MAX. AMB. °C	BRG.	L.S. 82070103
NO. FL. EFF.	NO.	O.S. 82050003

USABLE ON 208V NETWORKS AT **5.5** AMP.

GREASE ONLY

TOSHIBA INTERNATIONAL CORPORATION
 HOUSTON, TEXAS-MADE IN U.S.A.