

Fristam FP-Series Centrifugal Pump

Mfg: Fristam

Model: FP711-95

Stock No. NPPC154.

Serial No. FP711963332

Fristam FP-Series Centrifugal Pump. Model: FP711-95. S/N: FP711963332. Capacity: up to 56 gpm @ 3 psi and 7.5 head/ft. Impeller diameter: 4 in. (100 mm). Seal option: double mechanical seals. Baldor Industrial Motor, 1/2 hp, 1725 rpm, 208-230/460 V, 1.8-1.6/.8 amps, 60 Hz, 3 phase. FP-Series centrifugal pumps are able to process abrasive products, are CIP-able and SIP-able, and are capable of product temperatures up to 400 °F. Inlets: (1) 2 in. s-line. Outlets: 1-1/2 in. s-line discharge. Overall dimensions: 23 in. L x 9 in. W x 14 in. H.



