

Stainless Steel Shell and Tube Heat Exchanger

Mfg:

Model:

Stock No. OI239.

Serial No.:

Stainless Steel Shell and Tube Heat Exchanger. Contact surface area: 268 sq. ft. Number of tubes: 54. Tube dimensions: 2 in dia. x 114 in. L. Carbon steel shell. Inlets: (1) 20 in. dia., 24-bolt flange, (1) 8 in. dia., 8-bolt flange. Outlets: (1) 8 in. dia., 8-bolt flange, (1) 2-1/2 in. dia. S-Line port. Overall dimensions: 13 ft. 7 in. L x 36 in. W x 36 in. H.



