

## Baldor Motor – 25 hp

**Mfg: Baldor**

**Model:**

**Stock No.: MDBC266A**

**Serial No.: 0599C**

Unused Baldor Electric Motor- 25 HP. Cat No: M4103T. S/N: 0599C. Motor specifications: 1760 rpm, 230/460 V, 60/30 amps, 60 Hz, 3 phase. Frame: 284T. Continuous duty. Insulation class: F. Code: G. Maximum ambient temperature: 104°F (40°C). Enclosure: TEFC. Estimated weight: 342 lbs. Overall dimensions: 2 ft. 3 in. L x 1 ft. 7-1/2 in. W x 1 ft. 5 in. H. (ACN16a)

