

Gas Fired 48-Burner Stainless Steel Tunnel Oven - 24 in. Wide

Mfg:

Model:

Stock No: PMHT01

Serial No:

Gas Fired Tunnel Oven with 24 upper and 24 lower burners. Belt width: 24 inches. Product clearance: 2.75 in. Conveyor belt gap: 0.5 in. Burner specs: Asia Infra-Red Burner Type A-1601 (Taiwon). Gas consumption rates (per burner): 0.45 kg/hr with LPG / 0.49 m³/hr NGV. Heat: 5,400 kcal/hr (per burner). Tunnel has stainless steel construction. There is no nameplate or brand name listed on the tunnel. Previously installed in a fish cooking application in Texas. Conveyor infeed / outfeed length: 45 in. / 12 in. Oven conveyor length: 141 in. Conveyor features a tensioning adjustment and cleaning dip-tank. Mechanical vari-speed drive is adjustable. Motor: Dayton model 3N297A, 0.5 HP, 230/460V, 3-phase, 60Hz. Includes a Square D Telemecanique model Altivar 16 motor controller, which will ship loose without an enclosure. Overall length: 17 ft. 2 in. L.

