

Gas Fired 24-Burner Stainless Steel Tunnel Oven - 24 in. Wide

Mfg:

Model:

Stock No: PMHT05

Serial No:

Gas Fired Tunnel Oven with 24 burners mounted above the belt. Belt width: 24 inches. Product clearance in oven area: 2.75 in. Conveyor belt gap: 0.5 in. Burner specs: Asia Infra-Red Burner Type A-1601 (Taiwan). Gas consumption rates (per burner): 0.45 kg/hr with LPG / 0.49 m³/hr NGV. Heat: 5,400 kcal/hr (per burner). Tunnel has stainless steel construction. There is no nameplate or brand name listed on the tunnel. Previously installed in a fish cooking application in Texas. One end of conveyor features an air-knife blower, conveyor dip with roller, and second air blower. Features a cleaning dip tank for conveyor. Mechanical vari-speed drive is adjustable. Motor: Dayton model 3N297A, 0.5 HP, 230/460V, 3-phase, 60Hz. Includes a Square D Telemecanique model Altivar 16 motor controller, which will ship loose without an enclosure. Oven area is approximately 11 ft. 9 in. L. Overall length: 17 feet.

