

Fristam FP-Series Centrifugal Pump

Mfg: Fristam

Model: FP721-140

Stock No. NPPC151.

Serial No. FP210011004

Fristam FP-Series Centrifugal Pump. Model: FP721-140. S/N: FP210011004. Capacity: up to 68 gpm at 8 psi and 17 head/ft. Impeller diameter: 5-1/2 in. (140 mm). Baldor Industrial Motor, 3 hp, 1725 rpm, 230/460 V, 8.2/4.1 amps, 60 Hz, 3 phase. FP-Series centrifugal pumps are able to process abrasive products, are CIP-able and SIP-able, and are capable of product temperatures up to 400 °F. Outlets: 1-1/2 in. S-line discharge. Overall dimensions: 24 in. L x 11 in. W x 12 in. H.



