

Hoeksma & Velt-Leeuwarden Stainless Steel Butter Trolley - 115 Gallons

Mfg: Hoeksma & Velt-Leeuwarden

Model:

Stock No. RCCB260.34

Serial No.:

Hoeksma & Velt-Leeuwarden Stainless Steel Butter Trolley - 115 Gallons. Order No. 006.168. (2) Screw Augers dimensions: 10 in. dia. 65 ½ in. L. SEW Euro-drive Motor: 1700 rpm, 230/460 V, 8.6/4.2 amps, 60 Hz. 3 phase, Ratio: 71.32, Rpm: 1700 in, 24 out. Torque: 5430. Crepaco Positive Displacement Pump. Model: R6RIHD. S/N: B-5662. SEW Variable Speed Drive, 7.5 hp, 1750 rpm, 230/460 V, 19.2/9.6 amps, 60 Hz, 3 phase. Euro-Drive, 845-3533 input rpm, 31-133 output rpm. Ratio 26.84. Final rpm: 65. Torque: 2830 lb-in. Outlets: (1) 2 in. dia. NPT (male), (1) 3 in. dia. S-Line. Pump dimensions: 4ft. 10 in. L x 4ft. 1 in. W x 6ft. 7 in. H. Butter trolley dimensions: 7ft. 3-1/2 in. L x 4ft. 5-1/2 in. W x 3ft. 3-1/2 in. H. Utilizing two, horizontal screws to remove and convey butter off-loaded from conventional churns or continuous butter makers, other food handling applications of the butter trolley include: baking fats, cocoa butter, mayonnaise or creams. The screw augers provide for minimal product contact and sanitary handling of the product to the packaging machine. Overall dimensions: 11 ft. 3 in. L x 6 ft. W x 6 ft. 9 in. H.









