

Ingersoll-Rand H-HC Centrifugal Pump

Mfg: Ingersoll-Rand

Model: 4x3x6H


Stock No.: RGMP404B

Serial No.: 0979/4579

Ingersoll-Rand Centrifugal Pump. S/N: 0979/4579. Type: H-HC. Size: 4x3x6H. Impeller diameter: 4-3/4 in. Capacity: 360 gpm @ 65 tdh. U.S. Electric Motor, 10 hp, 3500 rpm, 230/460 V, 26/13 amps, 60 Hz, 3 phase. Inlets: (1) 4 in. dia. flanged port. Outlets: (1) 3 in. dia. flanged port. Overall dimensions: 2 ft. 3-1/2 in. L x 1 ft. 3 in. W x 1 ft. 2-1/2 in. H.







1971-2071
READ INSTRUCTION BOOK BEFORE OPERATING PUMP
Ingersoll-Rand
 STANDARD PUMP - ALDRICH DIVISION
 CENTURY II[®] Type **H-HC** Pump
 Pump Size **4X3X6H**
 Serial No. **0979/4579**
 RPM **3600** GPM **50**
 TOT. HD. FT. **65**

UNICLOSED MOTOR 191733

HP	TO	PH	480	15HZ	60	115 VOLTS
FRAME	213TC		180		2670	200
TYPE	A		460		1870	200
TEMP.	40°C MAX. AMB.					LINE
DESIGN	6309-J/03	RPM	3500			SF
	6808-07-J/03	SF	1.15			
DESIGN B CODE # 63-07247-609 BT1488						MINIMUM POWER SYSTEM VOLTAGE 240-480

SELF-LUBRICATED FOR LONGEST LIFE BE LUBRICATED BEARRINGS YEARLY AS FOLLOWS: 1. REMOVE DRAIN PLUG + INJECT NEW GREASE AT 72.2 INCHES • RUN MOTOR FOR 5 MINUTES • REPEAT UNTIL GREASE IS VISIBLY EXHAUSTED • REPLACE DRAIN PLUG

U.S. ELECTRICAL MOTORS
 DIVISION OF EMERSON ELECTRIC - MILFORD, CONN.