

**Frigoscandia FloFREEZE IQF Tunnel - 10MA**

**Mfg: Frigoscandia**

**Model: FloFreeze 10MA**

**Stock No: RPCA1300.40**

**Serial No: 00312091**

Frigoscandia IQF Tunnel. Model: FloFREEZE 10MA. S/N: 00312091. Nominal Capacity: 11,550 lbs/hour (5,250 kg/hour). Commonly used with peas, cut vegetables, berries, cut fruits, French fries, meats, etc. Fluidized design uses upward air flow that conveys the product without the need for a belt conveyor. This design also completely surrounds the product with low temp air for quick freezing with minimal clumping. Product must be de-watered prior to entering the FloFREEZE unit. Dimensions: 28 ft. L x 8 ft. W x 12 ft. H. Last used with a Key stainless steel frame vibratory feed conveyor 8 ft. L x 22 in. W. Last used with ammonia refrigerant.







