

Volumetric Screw Feeder

Mfg:

Model:

Stock No. OI191.

Serial No.:

Volumetric Screw Feeder. (2) Screw augers. (1) Ribbon blender. Lower screw auger: 2 in. dia. x 18-1/2 in. L. Underwriter Laboratories Motor, 1-1/2 hp, 1725 rpm, 575 V, 2a amps. Upper screw auger: 7 in. dia. x 16 in. L. WEG Motor, 5 hp, 1740 rpm, 575 V, 5.6 amps, 60 Hz. Dodge Gear Drive, 15.55 Ratio, 112 rpm (final). Ribbon blender: 14 in. dia. x 16 in. L. Inlets: (1) 10 in. x 10 in. infeed with (12) 1/4 in. bolt holes. Outlets: (1) 2 in. NPT fitting. Overall dimensions: 67 in. L x 65 in. W x 61 in. H.



