

## Howe Corporation Ammonia Receiver System - 69 Gallon

**Mfg: Howe**

**Model:**

**Stock N.: RPCN505**

**Serial No: 5617, 5618, 5619**

Howe Corporation Ammonia Receiver System. S/N's: 5617, 5618, 5619. Nat'l Bd: 4907, 4908, 4909. Cat. No's/Dwg. No's: PVL277A, PVL277B, PVL277C. Top Receiver- 30 Gallon, inside straight-wall dimensions: 1 ft. 3 in. dia. x 3 ft. 6 in. L. Middle Receiver- 9 Gallon, inside straight-wall dimensions: 1 ft. dia. x 1 ft. 8 in. H. Bottom Receiver- 30 Gallon, inside straight-wall dimensions: 1 ft. 3 in. dia. x 3 ft. 6 in. L. MAWP: 250 psi @ 650°F. (2) Hansen Technologies Fluid Float Switches. Gulf & Western Manufacturing Co. Transfer Timer. Inlets/Outlets: (2) 3 in. dia. ports, (2) 1/2 in. dia. port, (2) 1 in. dia. ports, (1) 1-1/2 in. dia. port. Overall dimensions: 5 ft. 9 in. L x 4 ft. 2 in. W x 8 ft. 7 in. H.





