

Tri Clover Centrifugal Pump

Mfg: Tri Clover

Model: C4410SD25TT-70ND-01U-08IN

Stock No. SFEP195K.5

Serial No. 583045-01

Tri Clover Centrifugal Pump. Model: C4410SD25TT-70ND-01U-08IN. S/N: 583045-01. Pump capacity: 440 gpm. Reliance electric motor, 15 hp, 1765 rpm, 230/460 V, 36.2/18.1 amps, 60 Hz, 3 phase. Pump inlet/outlet: 4 in. $\frac{1}{2}$ line. Typical beverages applications; carbonated soft drinks (final product), fruit juice, wine, cider, coffee and tea, still water, drinking water. Typical food applications: condiment sauces, soups, vegetable and pressed oils, vinegar, desserts, whey transport. Overall dimensions: 35 in. L x 20 in. W x 25 in. H.



