

## Votator Agitated Holding Unit

Mfg:

Model:

Stock No. OI245.

Serial No.:

Votator Agitated Holding Unit. Shaft dimensions: 4 in. dia. x 16 in. L. Consists of a tube, in which a shaft with agitating pins revolves at a fixed speed; the unit prevents margarine from "setting," so it can deliver the soft product to tubs or bulk containers. U.S. Motor, 1/2 hp, 1720 rpm, 208-220/410 V, 2.75-2.6/1.3 amps, 60 Hz, 3 phase. U.S. Varidrive Module, 190 rpm (min), 1900 rpm (max). Inlets/outlets: (2) 1/2 in. dia. MPT. Overall dimensions: 47 in. L x 17-1/2 in. W x 29-1/2 in. H.



