

## Precision Screw Feeder for Dry Ingredients

**Mfg: N/A**

**Model:**

**Stock No.: SKFI048.11**

**Serial No.:**

Dry Ingredients Precision Screw Feeder, Leeson Washguard Motor, ½ hp, 1725 rpms, 208-230V, 3 phase, Dodge gear reducer with 17.1 gear ratio, final rpms: 100. Unit is speed controlled using Magnetek GPD333 VFD. Oval outlet dimensions: ¾ inches long x 3/8 inches wide. Overall dimensions: 72 in. x 36 in. x 70 in. High.

Magnetek GPD333-A001N4, spec 20P7D8, S/N: N7P1391-3-8, UL listed. AC input: 200-230V, 50-60 Hz, 5.5 Amps, 3-phase, IP56 Type 4 Enclosure. AC output: 0-230V, 0-400 Hz, 3-phase, 1 HP, 5 amps.





