

Vibra Screw Incorporated Volumetric Live Bin Screw Feeder 2.3 to 23 Cu. Ft/Hr

Mfg: Vibra Screw Incorporated

Model: K 1308

Stock No. SLTN019.1a

Serial No. 701505

Vibra Screw Incorporated Volumetric Live Bin Screw Feeder- 92 to 920 Lbs/Hr (2.3 to 23 Cu. Ft/Hr). Model: K 1308. S/N: 701505. Stainless steel 20 in. dia. live bin with a capacity of 3 cu. ft. Screw auger diameter: 2 in. Vibrating Platform. Baldor DC Motor, 0.75 hp, 1750 rpm. 90 V, 7.0 amps. Dodge Speed Reducer, ratio: 6.2, final speed: 282 rpm, torque: 257 in-lbs. This combination produces an extremely efficient, accurate and dependable feeder for an almost infinite variety of dry materials: chemicals, foods, plastics, pharmaceuticals, metal powders, minerals, and similar materials. Outlets: (1) 6 in. dia. chute. Overall Dimension: 36 in. L x 20 in. W x 32 in. H.



