

ITT AC Centrifugal Pump

Mfg: ITT

Model: 150

Stock No. SMBV005.

Serial No. _____

ITT AC Centrifugal Pump. Model: 150. Type: 2000. Capacity: 150 gpm @ 52 TDH. Max field hydrotest pressure: 175 psi. Siemens Motor, 5 hp, 3490 rpm, 230/460 V, 11.6/5.8 amps, 60 Hz, 3 phase. Inlets: (1) 2-1/2 in. dia. port with an X-pattern flange with (4) 1/2 in. bolt holes. Outlets (1) 2 in. dia. port with a 6 in. flange and (4) 1/2 in. bolt holes, (1) 1/2 in relief valve. Overall dimensions: 44 in. L x 13 in. W x 22 in. H.

