

Stainless Steel Centrifugal Pump

Mfg:

Model:

Stock No. OIP118.

Serial No.:

Stainless Steel Centrifugal Pump. Impeller diameter: 4 in. General Electric Motor, 2 hp, 3450 rpm, 200-230/460 V, 5.8-5.4/2.7 amps, 60 Hz, 3 phase. Inlets: (1) 2 in. dia. ACME fitting. Outlets: (1) 1-1/2 in. dia. ACME fitting. Overall dimensions: 1 ft. 8 in. L x 9 in. W x 8 in. H.



