

Goulds Sanitary Centrifugal Pump

Mfg: Goulds

Model: 3196

Stock No. OIP154.

Serial No. 754C253.7

Goulds Sanitary Centrifugal Pump. Model: 3196. S/N: 754C253.71. Size: 1.5x3-10. Material of Construction: 316 Stainless Steel. Nominal Capacity: 140 gpm. Displacement per Revolution: 0.079 gal. Impeller diameter: 8-13/16 in. Maximum Solid Size: 0.219 in. Reliance Electric Motor: 15 hp, 1760 rpm, 230/460 V, 40/20 amps, 60 Hz, 3 phase. Introduced in 1961 as the original Goulds 3196 ANSI Standard Dimension Process Pump, the Goulds 3196 quickly became the top selling pump of its kind worldwide. It continues to be recognized as a workhorse in chemical, petrochemical, pulp and paper, primary metals, food and beverage, and general-industry processes. Overall dimensions: 4 ft. 2 in. L x 1 ft. 8 in. W x 2 ft. 2 in. H.



