

### 4 ft. Conveyor Section with Reject Mechanism

Mfg:

Model:

Stock No. SNBB249.

Serial No.

4 ft. Conveyor Section with Reject Mechanism. Belt dimensions: 48 in. L x 12 in. W, has 2 sensors and a pneumatically operated reject mechanism. Baldor motor, 5 hp, 1,725 rpm, 208-230/460 V, 1.9/.9 amps, 60 Hz, 3 phase. Overall dimensions: 62 in. L x 55 in. W x 33 in. H. Ideal for placement immediately after metal detectors and checkweighers for defective product ejection.

