

Sanitary Centrifugal Pump

Mfg:

Model:

Stock No. OIP157.

Serial No.:

Sanitary Centrifugal Pump. 316 stainless steel construction. Impeller diameter: 6 in. Baldor Industrial Motor, 10 hp, 3450 rpm, 208-230/460 V, 23.3-24/12 amps, 60 Hz, 3 phase. Inlet: (1) 2-1/2 in. dia. S-line fittings. Outlet: (1) 2 in. dia. S-line fittings. Overall dimensions: 2 ft. L x 11 in. W x 1 ft. 2 in. H.



