

FMC Single Bar Grader

Mfg: FMC

Model:

Stock No.: SNPM108.1a

Serial No.: H1-170

FMC Single Bar Grader. S/N: H1-170. Inside straight-wall dimensions: 1 ft. 7-1/2 in. dia. x 2 ft.10 in. L. Infeed barrel dimensions: 2 ft. dia. x 1 ft. 8 in. L. U.S. Electrical Syncrogear motor, 1/2 hp, 1745 rpm, 230/460 v, 2.06/1.03 amps, 60 Hz, 3 phase. Syncrogear drive, ratio: 6.1, rpm out: 286 (final). Inlets: (1) 1 ft. 2 in. dia. port (product in). Outlets: (1) 11 in. dia. port (discharge), (1) 1 ft. 3 in. L x 1 ft. 1-1/2 in. W. (product out). Overall dimensions: 6 ft. 11 in. L x 3 ft. 2 in. W x 4 ft. 4 in. H.



