

Cherry-Burrell Sanitary Centrifugal Pump

Mfg: Cherry-Burrell

Model: 4BHK-F

Stock No. OIP158.

Serial No. 5122

Cherry-Burrell Sanitary Centrifugal Pump. Model: 4BHK-F. S/N: 5122. Impeller diameter: 6 in. Electric Motor, 20 hp, 3500 rpm, 230/460 V, 46/23 amps, 60 Hz, 3 phase. Inlet: (1) 2 in. dia. ACME fitting. Outlet: (1) 2 in. dia. ACME fitting. Overall dimensions: 2 ft. 7 in. L x 1 ft. W x 1 ft. 3 in. H.

