

Refrigerated Stainless Steel Mixing Tank-100 gallons

Mfg:

Model:

Stock No. SSLP200.2

Serial No.:

Refrigerated Stainless Steel Mixing Tank-100 Gallon. Agitator drive, type: SP, 36 rpm, 120 in. lb., 230 V, 1 amp. Shaft dimensions: 1 in. dia. x 26-1/2 in. L. Propeller dimensions: 20 in. L x 5-1/2 in. W. Refrigeration system capacity: 1/2 ton; refrigerant 401A. Power: 230 V, 60 cycles, 3.7 FLA air, 3.7 FLA water, 22.5 LRA. Condenser dimensions: 13 in. x 12-1/2 in. Temperature gauge: 0-100 °F. Base with (4) casters. Inlet (top): 7-1/4 in. dia. Tank opening: 2 in. threaded male. Overall dimensions: 80 in. L x 50 in. W x 64 in. H.





