

Arrowhead Table Top Conveyor System - 4.5" wide

Mfg: Arrowhead Conveyor

Model:

Stock No.: SUBF261.2a

Serial No.:

- Arrowhead Table Top Conveyor with 90° Elbow. Material construction: stainless steel. Maximum aperture: 4-1/2 in. W. Infeed/exit height: 10 in. Overall dimensions: 7 ft. 1 in. L x 3 ft. W x 1 ft. 4-3/4 in. H.
- Arrowhead 90° Elbow Table Top Conveyor. Material construction: stainless steel. Maximum aperture: 4-1/2 in. W. Infeed/exit height: 9-3/4 in. Overall dimensions: 3 ft. L x 2 ft. 9 in. W x 1 ft. 6 in. H.
- Arrowhead Table Top Conveyor. Material construction: stainless steel. Maximum aperture: 4-1/2 in. W. Infeed/exit height: 9-3/4 in. Overall dimensions: 3 ft. 10-1/4 in. L x 1 ft. 1-3/4 in. W x 1 ft. 3 in. H.
- Arrowhead Table Top Conveyor. Material construction: stainless steel. Maximum aperture: 4-1/2 in. W. Infeed/exit height: 9-1/2 in. Overall dimensions: 5 ft. 3-1/2 in. L x 1 ft. 1-3/4 in. W x 1 ft. 1-1/2 in. H.
- Arrowhead Table Top Conveyor. Material construction: stainless steel. Maximum aperture: 4 in. W. Infeed/exit height: 9-1/2 in. Overall dimensions: 10 ft. 2 in. L x 1 ft. 1 in. W x 1 ft. 3 in. H.
- MCC Max-line Straight Run Single Hinge Slat Band Conveyor Chain. Type: 60S31SM. Quality: Slide line. Code Nr: 762.6931. Chain width: 3-1/4 in. Working load: 6000 N. Flatness: +/- .10 mm. Gap: 1.6 mm. Minimum back flex radius: 150 mm. Surface finish (max): .30 µm. Overall dimensions: approx. 44 ft. L x 3-1/4 in. W.







