

**McHale Manufacturing Co. Pre-mix Tank with Tri Clover PR10 Positive Displacement Pump-100 Gallons**

**Mfg: McHale Manufacturing**

**Model: 857**

**Stock No: RCPK525.2a**

**Serial No: 2836**

McHale Manufacturing Pre-mix Tank with Tri Clover PR10 Positive Displacement Pump. Model: 857. Approximate capacity: 100 gallons. Model: 857. S/N: 2836. Inside straight-wall dimensions: 2 ft. 6 in. dia. x 2 ft. 11 in. H. Tri-Cover PR10 Positive Displacement Pump, Model: PR10-1-1/2-TC1-4-ST-S, S/N: R2997, capacity: 8.55 gpm, seal option: O-ring seals. Sterling Electric Motor, 1 hp, 1140 rpm, 208-230/460 V, 3.5-3.4/1.7 amps, 60 Hz, single phase, pulley ratio: 2 to 1, final rpm: 570. Start/stop control switch. Mounted on frame with (4) casters for easy positioning. Inlets: (1) 1-1/2 in. dia. ACME fitting (pump suction). Outlets: (1) 1-1/2 in. dia. ACME fitting (pump discharge), (1) 2 in. dia. ACME fitting (tank discharge). Overall dimensions: 4 ft. 2 in. L x 4 ft. W x 4 ft. 3 in. H.









