

## Stainless Steel Single Shell Tank With Lightnin Mixer

Mfg:

Model:

Stock No. RDGZ02.

Serial No.

Stainless Steel Single Shell Tank With Lightnin Mixer. Pneumatic Mixer Model: XDA-33, S/N: 89/525043-01, 1/3 hp, air pressure: 60 psi. Gear driven for maximum output torque, propeller diameter: 4 in., shaft: 15-1/2 in. Pneumatic mixers are safe for use in flammable or explosive environments. No heat build-up. Motor operates spark free. Speeds can be varied by means of the air control valve. Motor designed to handle stalling overloads without burning out. Lightweight makes for easy handling. Tank capacity: 18 gallon. Tank inside dimensions: 15 in. dia. x 23 in. H. Inlets/outlets: (2) 2 in. threaded female, (2) 2-1/4 in. threaded female. Overall dimensions: 24 in. L x 20 in. W x 39 in. H.

