

## M.G. Newell Corporation Barrel Dumping Central Crusher Unit

**Mfg: M.G. Newell Corporation**

**Model:**

**Stock No: TABF01**

**Serial No:**

M.G. Newell Corporation Barrel Dumping Central Crusher Unit. Job no. 300732/300248. Capable of running one 55-gallon barrel per minute of frozen concentrate. Pneumatic air cylinder : Model no. P1AU-18A1E-G2A0. M.G. Newell Corporation Control Panel. Job Number: 300248. Overall control panel dimensions: 3 ft. 7-1/2 in. L. x 3 ft. 3-1/4 in. W. x 1 ft. 2-5/8 in. H. Power supply starter panel dimensions: 3 ft. 1-5/8 in. L. x 2 ft. 7-5/8 in. W. x 11 in. H. (2) Pressing rollers: 1 ft. 8 in. L. x 6 in. dia. Sprockets for rollers: 3-1/2 in. driver, 5 in. driven. Baldor Electric motor: 10 Hp, 1760 Rpm, 208-230/460 V, 28.5-28.4/14.2 A, 60 Hz, 3 Phase. Baldor Electric motor: 5 Hp, 1725 Rpm, 230/460 V, 1.6/8 A, 60 Hz, 3 Phase. Auger dimensions: 4 ft. x 1 ft. 9 in. dia. 2 in. x 2 in. teeth grinders. 1 in. screen size dia. (1) Input product dumping dimensions: 9 ft. 8 in. L. x 4 ft. 4-1/2 in. W. (1) 3-7/8 in. output flange dia. (8) 3/4 in. mounting holes dia. 2-7/8 in. adjacent, 7-3/8 in. opposite. Overall dimensions: 11 ft. 8-1/2 in. L. x 7 ft. 6 in. W. x 7 ft. 8 in. H.















