

## 1996 Fristam Centrifugal Pump FPX Series

Mfg: Fristam

Model: FPX1161-320

Stock No. RLOL283.15

Serial No. FPX1161961560

1996 Fristam Centrifugal Pump FPX Series. Model: FPX1161-320. S/N: FPX1161961560. Capacity: 500 gpm @ 67 psi and 155 head/ft. Impeller diameter: 12 in. Baldor Industrial Motor, 30 hp 1750 rpm, 230/460 volts, 76/38 amps, 60 Hz, 3 phase. Capable of delivering high volumes and high pressures while handling shear sensitive products, it is the pump of choice for products with viscosities up to 600 cps and process temperatures up to 400°F. The FPX series is well known for quiet and efficient, low maintenance operations. Inlets/outlets: (2) 4 in. S-line fittings. Overall dimensions: 3 ft. 1 in. L x 1 ft. 10 in. W x 1 ft. 9 in. H.



