

Cherry Burrell Stainless Steel Refrigerated Tank-1,500 Gallons

Mfg: Cherry Burrell

Model: FHW

Stock No. HDFI91.8

Serial No. 15-FHW-62-1586

Cherry Burrell Stainless Steel Refrigerated Tank-1,500 Gallons.

- Model FHW. S/N 15-FHW-62-1586.
- Inside dimensions: 66 in. dia., 114 in. length.
- Inlets (2) 3 in., 1-½ in. for spray ball.
- Outlets (1) 2 in. 6 legs 6 in. high.
- Motor Master, Gear Motor. Identification 613585 - HL. Type PB, Frame: 203RW, 1 hp, 60 hz, 208/220/440 V, 3 phase, 1,740 rpm, 3/1.5 amps, cont. 55 °C. Temp rise, 54 Co-Shaft rpm. Code M .
- Overall dimensions 74 in. W x 126 in. L x 89 in. H.



