

Un-Used Baldor Motor- 20 HP

Mfg: Baldor

Model:

Stock No. RPAG1117.2a

Serial No. C0112120044

Un-Used Baldor Motor- 20 HP. S/N: C0112120044. Explosion proof. Motor specifications: 20 hp, 1775 rpm, 230/460 V, 49/24.5 amps, 60 Hz, 3 phase. Spec: 12E258X45461. Frame: 326T. Class B. Code: H. Design: B. Shaft diameter: 2-1/8 in. Stearns Brakes Motor Brake, Model: 108736100017, S/N: 81193D001, horizontal mounting, 230-460/190-380 V, 60 Hz. Overall dimensions: 44 in. L x 24 in. W x 20 in. H.



