




JOB:	REPRESENTATIVE:	
UNIT TAG:	ORDER NO.	DATE:
ENGINEER:	SUBMITTED BY:	DATE:
CONTRACTOR:	APPROVED BY:	DATE:



4BD

Series e-1510

Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW _____ HEAD _____

HP _____ RPM _____

VOLTS _____

CYCLE _____ PHASE _____

ENCLOSURE _____

APPROX. WEIGHT _____

SPECIALS _____

MATERIALS OF CONSTRUCTION

Stainless Steel Fitted

FEATURES

- ANSI/OSHA Coupling Guard
- Center Drop Out Spacer Coupling
- Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE

175 psi (12 bar) W.P.
w/ 125# ANSI flange drilling

TYPE OF SEAL


- Standard Seal (Buna-Carbon/Ceramic)
- F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- S Stuffing Box Construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- PF Stuffing Box Construction w/ Packing (Graphite Impregnated Teflon)

Note: Equipped with NEOPRENE coupling





JOB:	REPRESENTATIVE:	
UNIT TAG:	ORDER NO.	DATE:
ENGINEER:	SUBMITTED BY:	DATE:
CONTRACTOR:	APPROVED BY:	DATE:



4BD

Series e-1510

Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW _____ HEAD _____

HP _____ RPM _____

VOLTS _____

CYCLE _____ PHASE _____

ENCLOSURE _____

APPROX. WEIGHT _____

SPECIALS _____

MATERIALS OF CONSTRUCTION

Stainless Steel Fitted

FEATURES

- ANSI/OSHA Coupling Guard
- Center Drop Out Spacer Coupling
- Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE

175 psi (12 bar) W.P.
w/ 125# ANSI flange drilling

TYPE OF SEAL


- Standard Seal (Buna-Carbon/Ceramic)
- F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- S Stuffing Box Construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- PF Stuffing Box Construction w/ Packing (Graphite Impregnated Teflon)

Note: Equipped with NEOPRENE coupling





JOB:	REPRESENTATIVE:	
UNIT TAG:	ORDER NO.	DATE:
ENGINEER:	SUBMITTED BY:	DATE:
CONTRACTOR:	APPROVED BY:	DATE:



4BD

Series e-1510

Centrifugal Pumps - Base Mounted

SPECIFICATIONS

FLOW _____ HEAD _____
 HP _____ RPM _____
 VOLTS _____
 CYCLE _____ PHASE _____
 ENCLOSURE _____
 APPROX. WEIGHT _____
 SPECIALS _____

MATERIALS OF CONSTRUCTION

Stainless Steel Fitted

FEATURES

- ANSI/OSHA Coupling Guard
- Center Drop Out Spacer Coupling
- Fabricated Heavy Duty Baseplate


MAXIMUM WORKING PRESSURE

175 psi (12 bar) W.P.
w/ 125# ANSI flange drilling

TYPE OF SEAL


- Standard Seal (Buna-Carbon/Ceramic)
- F Standard Seal w/ Flush Line (Buna-Carbon/Ceramic)
- S Stuffing Box Construction w/ Flushed Mechanical Single Seal (EPR-Tungsten Carbide/Carbon)
- PF Stuffing Box Construction w/ Packing (Graphite Impregnated Teflon)

Note: Equipped with NEOPRENE coupling



Series e-1510 4BD Centrifugal Pump Submittal

B-880.24B



FLANGE DIMENSIONS IN INCHES (MM)			
	SIZE	THICKNESS	O.D.
Discharge	4" (102)	1-1/4" (32)	9-1/2" (241)
Suction	5" (127)	1-3/8" (35)	10-3/4" (273)

FLANGES ARE 125# ANSI - STANDARD

DIMENSIONS – Inches (mm)

STANDARD SEAL

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF ₁	HF ₂	HH	HL	HM MAX	HO	HP	Y	Z
"S" FRAME														
213T	14-5/8 (371)	34-5/8 (879)	37-3/4 (959)	12-3/4 (324)	12-7/8 (327)	28-5/8 (727)	-	3/4 (19)	4 (102)	18-5/8 (473)	20-3/4 (527)	3 (76)	5 (127)	7 (178)
215T	14-5/8 (371)	34-5/8 (879)	39-1/4 (997)	12-3/4 (324)	12-7/8 (327)	28-5/8 (727)	-	3/4 (19)	4 (102)	18-5/8 (473)	20-3/4 (527)	3 (76)	5 (127)	7 (178)
254T	14-5/8 (371)	39-3/8 (1000)	43 (1092)	12-3/4 (324)	12-7/8 (327)	33-3/8 (848)	-	3/4 (19)	4 (102)	19-5/8 (498)	20-3/4 (527)	3 (76)	5 (127)	7 (178)
"L" FRAME														
256T	16 (406)	46-1/2 (1181)	49-1/8 (1248)	14 (356)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	5-1/8 (130)	20-7/8 (530)	22 (559)	5 (127)	5 (127)	7 (178)
284TS	16 (406)	46-1/2 (1181)	48-1/2 (1232)	14 (356)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	5-1/8 (130)	22 (559)	22 (559)	5 (127)	5 (127)	7 (178)
286TS	16 (406)	46-1/2 (1181)	50 (1270)	14 (356)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	5-1/8 (130)	22 (559)	22 (559)	5 (127)	5 (127)	7 (178)
324TS	16 (406)	51-3/4 (1314)	51-7/8 (1318)	14 (356)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	5-1/8 (130)	23-1/8 (587)	22 (559)	5 (127)	5 (127)	7 (178)
326TS	16 (406)	51-3/4 (1314)	53-5/8 (1362)	14 (356)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	5-1/8 (130)	23-1/8 (587)	22 (559)	5 (127)	5 (127)	7 (178)
364TS	24 (610)	56 (1422)	55-1/4 (1403)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	5-3/4 (146)	26-3/4 (679)	24-1/2 (622)	6 (152)	5 (127)	7 (178)
365TS	24 (610)	56 (1422)	55-7/8 (1419)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	5-3/4 (146)	26-3/4 (679)	24-1/2 (622)	6 (152)	5 (127)	7 (178)
404TS	24 (610)	56 (1422)	58-1/8 (1476)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	5-3/4 (146)	28-3/8 (721)	24-1/2 (622)	6 (152)	5 (127)	7 (178)
405TS	24 (610)	56 (1422)	58-7/8 (1496)	16-1/2 (419)	21-1/2 (546)	44 (1118)	22 (559)	1 (25)	5-3/4 (146)	30 (762)	24-1/2 (622)	6 (152)	5 (127)	7 (178)

STUFFING BOX

MOTOR FRAME	HA	HB	HC MAX	HD	2HE	HF ₁	HF ₂	HH	HL	HM MAX	HO	HP	Y	Z
"L" FRAME														
213T	16 (406)	46-1/2 (1181)	44-1/2 (1130)	14 (356)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	5-1/8 (130)	19-7/8 (505)	22 (559)	5 (127)	5 (127)	7 (178)
215T	16 (406)	46-1/2 (1181)	46 (1168)	14 (356)	14 (356)	36-1/2 (927)	18-1/4 (464)	7/8 (22)	5-1/8 (130)	19-7/8 (505)	22 (559)	5 (127)	5 (127)	7 (178)
254T	16 (406)	51-3/4 (1314)	49-3/4 (1264)	14 (356)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	5-1/8 (130)	20-7/8 (530)	22 (559)	5 (127)	5 (127)	7 (178)
256T	16 (406)	51-3/4 (1314)	51-1/2 (1308)	14 (356)	14 (356)	41-3/4 (1060)	20-7/8 (530)	7/8 (22)	5-1/8 (130)	20-7/8 (530)	22 (559)	5 (127)	5 (127)	7 (178)

Dimensions are subject to change. Not to be used for construction purposes unless certified.
 Box type pumps should not be operated at 3500 RPM.



Xylem Inc.
 8200 N. Austin Avenue, Morton Grove, IL 60053
 Phone: (847)966-3700 Fax: (847)965-8379
 www.bellgossett.com
 Bell & Gossett is a trademark of Xylem Inc. or one of its subsidiaries.
 © 2016 Xylem Inc.