





LIQUID FEED DATA:
 2.10 GPM LIQUID AT SUCTION TEMPERATURE PUMPED TO
 3.70 PSIG ABOVE SUCTION PRESSURE AT LIQUID INLET.



STANDARD UNIT DATA:

CASING: STAINLESS STEEL
 PAN: STAINLESS STEEL
 INSULATED W/ STAINLESS STEEL COVER
 COIL CONSTRUCTION: HOT DIP GALVANIZED STEEL
 DESIGN PRESSURE: 250 PSIG
 SHIPPING WEIGHT: 2,090 LBS.
 NUMBER OF UNITS: 3
 COIL VOLUME: 3.39 CUBIC FEET
 REFRIGERANT R-717

PERFORMANCE DATA:

7.57 TONS
 34 SUCTION TEMPERATURE (°F)
 45 ROOM TEMPERATURE (°F)
 10,566 CFM AIR FLOW
 0" EXTERNAL STATIC (IN WATER)
 2 MOTOR QUANTITY
 460-3-60 MOTOR VOLTAGE
 1/2 MOTOR HP EACH (TEAO)
 1200 MOTOR SPEED (RPM)
 1.1 MOTOR FLA EACH

A		REVISED FLA	8/11/03	SDA	IMECO SO# 37065	FRICK SO# 281447
LTR		DESCRIPTION	DATE	BY		
DO NOT SCALE PRINT		ALL DIMENSIONS				
WORK TO DIMENSIONS		ARE ± 1/2"				
MODEL: ATRB-284XXW		DRAWN BY: SDA		DATE: 5/31/03		
DRAWING #: 370650600		PAGE: 1 OF 1				

Frigid Coil/Imeco
 YORK INTERNATIONAL
 AU-9, 10.11 45°F BEAN SHIPPING & GRADING