

Morrison Container Handling Solutions Bottle Conveyor System

Mfg: Morrison Container Handling Solutions

Model: C-09-10-12120-001


Stock No. SAF006a


Serial No. 95/12120 ORIENT/COMB

Morrison Container Handling Solutions Bottle Conveyor System. Model: C-09-10-12120-001. S/N: 95/12120 ORIENT/COMB. Maximum bottle size: 3 in. dia. x 6-1/2 in. H. Timing screw dimensions: (1) 5 in. dia. x 3 ft. 6 in. L, (4) 6 in. dia. x 3 ft. L, (1) 5 in. dia. x 2 ft. 7 in. L. Reliance Electric Motor, 2 hp, 1725 rpm, 208-230/460 V, 6.4-8.4/13.2 amps, 60 Hz, 3 phase. Morse Torq Gard Speed Reducer, 680 rpm (final). Reliance Electric Motor, 3/4 hp, 1725 rpm, 208-230/460 V, 2.2-2.2/1.1 amps, 60 Hz, 3 phase. Winsmith Speed Reducer, 30 ratio, 58.3 rpm (final). Reliance Electric Motor, 1 hp, 1725 rpm, 208-230/460 V, 2.8-2.8/1.4 amps, 60 Hz, 3 phase. Winsmith Speed Reducer, 30 ratio, 58.3 rpm (final). (2) Bodine Electric Gear motor, 1/4 hp, 62 rpm (final), 130 V, 1.8 amps, 40 ratio. (2) Hub City Gear Drives. Gast Vacuum Pump, Model: 0765-V6A. Baldor Industrial Motor, 0.33 hp, 1725 rpm, 208-230/460 V, 1.8-1.6/0.8 amps, 60 Hz, 3 phase. Conveyor infeed/exit height: 42 in. Overall dimensions: 10 ft. 5 in. L x 5 ft. 4 in. W x 5 ft. 10 in. H.









MORRISON TIMING SCREW COMPANY

FOR CONNECTION TO MAIN PANEL OF
ORIENTOR/COMBINER ONLY

SEE DRAWING E-189-CA TO CE FOR ELECTRICAL
CONNECTIONS

TORQUE ALL TERMINALS TO 4.7-6.2 IN-LB.

