

Pama Roma Extruder

Mfg: Pama Roma

Model:

Stock No. SAPM031.2

Serial No.

Pama Roma Extruder. 3-compartment blender for efficient batch transfer. Outside compartments min/max capacity: 275/804 cu. in. Middle compartment min/max capacity: 53/154 cu. in. Number of paddles: 10. Paddle dimensions: 3 in. L x 1-1/2 in. W. Extruder diameter: 4 in. Number and size of perforations: (30) 1/8 in. dia. Mezmohejnice Motor, 1.1 kW/1.5 hp, 1,410 rpm, 380/220 V, 2.8-4.8 amps. Bonfiglioli Motor Drive, 1:23 ratio, 74.34 rpm (final). Inlets: (1) 19-1/2 in. L x 12-1/2 in. W infeed, (2) 1/4 in. dia. barb fittings (vacuum), (2) 4 in. W x 2 in. H side entry doors. Outlets: Extruder. Overall dimensions: 26 in. L x 25 in. W x 58 in. H.





