

Elevated Stainless Steel Belt Conveyor

Mfg:

Model:

Stock No. SDYC011.

Serial No.:

Elevated Stainless Steel Belt Conveyor. Belt width: 10 in. Conveyor features adjustable side guiderails and (4) casters for easy positioning. Infeed/exit height: 37/50 in. U.S. Motor, 1 hp, 1750 rpm, 208-230/460 V, 3.3-3.4/1.7 amps, 60 Hz, 3 phase. Syncogear Motor Drive, 84 rpm (final). Overall dimensions: 98 in. L x 26 in. W x 52-1/2 in. H.

