

Stainless Steel Steam Jacketed Kettle with Scraped Surface Agitator- 50 Gallon

Mfg:

Model:

Stock No. SFF365B.

Serial No.

Stainless Steel Steam Jacketed Kettle with Scraped Surface Agitator- 50 Gallon. Inside dimensions: 26 in. dia. x 26 in. H. Shaft diameter: 1-1/2 in. (2) Scrapers: 4 in. L x 3 in. W. Agitator diameter: 22 in. Reliance Electric Motor, 1 hp, 1140 rpm, 208-230/460 V, 3.4-3.4/1.7 amps, 60 Hz, 3 phase. Dodge Tigear 2 Speed Reducer, ratio: 60, final speed: 19 rpm, max torque out: 1547 lb-in. Inlets: (1) 26 in. dia. open top, (1) 1 in. dia. FNPT (media). Outlets: (1) 2 in. dia. S-line fitting, (1) 1/2 in. dia. FNPT (media). Overall dimensions: 3 ft. 1 in. L x 2 ft. 5 in. W x 4 ft. 7 in. H.



