

1999 Bryan 150 HP Water Tube Steam Boiler

Mfg: Bryan

Model: RV-05150S150FDG

Stock No. pHDHP140.5

Serial No. 84918

1999 Bryan 150 HP Water Tube Steam Boiler. Model: RV-05150S150FDG. S/N: 84918. "Ohio Special" boiler with a maximum of 358 sq. ft. of heating surface. Capacity: 5,000 pph. Steam design pressure: 150 psig. Complete with Power Flame Burner flame retention head type burner for forced draft. Flame retention head type burner provides efficient combustion of oil or gas and ensures quiet operation, Model: CR4-G-30, S/N: 119991942, gas type: natural gas, opening time: 13 sec, max. closing time: 1 sec. Baldor Industrial Motor, 5 hp, 3450 rpm, 208-230/460 V, 13.2-12/6 amps, 60 Hz, 3 phase. Inlets: (1) 3-1/2 in. dia. inlet with a 14 in. dia. flange and (8) 3/4 in. dia. attachment holes, (1) 16 in. dia. inlet with 19-3/4 in. dia. flange and (16) 1/2 in. dia. attachment holes. Outlets: (1) 3/4 in. dia. FPT, (1) 1 in. dia. pipe, (2) 1 in. dia. MPT, (1) 1-1/2 in. dia. FPT, (1) 2 in. dia. threaded fitting. Overall dimensions: 13 ft. 8-1/2 in. L x 58 in. W x 9 ft. 5 in. H. (2) Honeywell Pressure Trol. (1) Honeywell Operating Pressure Trol. (1) Guard Dog low-water cutoff control unit, Model: 750.



