

Frick Rotary Vane Booster Compressor - 200 HP

Mfg: Frick

Model:

Stock No.: sEELD669.1a

Serial No.:

Frick Rotary Vane Booster Compressor – 200 HP. Frick Oil Separator- 50 Gallon, Nat'l Bd: 39374, Material SA: 53. T.S: 60,000, straight-wall dimensions: 1 ft. 4 in. dia. x 5 ft. 3 in. L, MAWP: 150 psi @ -20 to 300°F, shell thickness: 0.375 in., head thickness: 0.215 in., radius: 2:1. Frick Oil Cooler, S/N: PC75020, shell side MAWP: 150 psi @ -20 to 200°F, shell thickness: 0.277 in., head thickness: 0.94 in., radius: flat, tube side MAWP: 150 psi @ -20 to 200°F, shell thickness: 0.277 in., head thickness: 0.5 in., radius: flat. Westinghouse Electrical Motor, 200 hp, 1775 rpm, 460 V, 226 amps, 60 Hz, 3 phase, pulley ratio: 1.68, final rpm: 1057. Frick Control Panel, Code Ident. No: 23587. (2) Hansen Technologies Relief Valves, S/N: 053, Cat. No: H5600R, capacity: 150 scfm, max pressure: 150 psi. Inlets: (1) 6 in. dia. port, (1) 1 in. dia. port, (1) 1/2 in. dia. port. Outlets: (1) 5 in. dia. flanged discharge port, (1) 1-1/4 in. dia. port, (1) 1 in. dia. port. Overall dimensions: 8 ft. 2 in. L x 7 ft. 6 in. W x 6 ft. 9 in. H.







