

## 1998 Ozocan Corporation Ozotec™ Type S Ozone Generating System

**Mfg: Ozocan Corporation**

**Model: 7**

**Stock No: SGMM141.25**

**Serial No: 98205-01-HA2145**


1998 Ozocan Corporation Ozotec™ Type S Ozone Generating System. Model: 7. S/N: 98205-01-HA2145. Capacity: 2mg/L to a flow rate of 100 gpm resulting in a residual of around 0.4 mg/L after mixing in the contact tank for a minimum of 4 minutes. Ozone capacity: 2.8 lbs. per day. Cooling water flow requirements: 40 gph. Power supply requirements: 575 V, 10 amps, 60 Hz, 3 phase this is stepped down to 230 V, 10 amps, 60 Hz. single phase. Unit features 2 centrifugal pumps. Recirculation pump 1: 316 stainless steel, with a 1 hp, 575 V, 2 amps, 60 Hz, 3 phase motor. Process pump 2: 316 stainless steel, 3 hp, 575 V, 7 amps, 60 Hz, 3 phase motor. Gast air compressor model: 7HDD-11T, 230 V, 10 amps, 60 Hz, single phase, with a 30 gal. air receiver. 75 gal. Reservoir tank, MAWP: 10 psi at 130°F. The Ozotec™ Type S ozone generating system covers a wide range of applications to include drinking water disinfection and the removal of unwanted odors, colors and tastes, waste water disinfection and heavy metal oxidation. Overall dimensions: 14 ft. 2 in. L x 7 ft. 9 in. W x 9 ft. 6 in. H.















MFG.: HANKIN OZONE  
MODEL#: #7  
SERIAL#: 98205-01-HA2145  
VOLTAGE: 110V 1PH  
AMPERAGE: 10A  
SOURCE: FED FROM  
PACKAGING RM. PANEL  
CIRCUIT 6

