

APV R3BS Positive Displacement Pump and Balance Tank Skid

Mfg: APV

Model: R3BS

Stock No. tLXBK003.

Serial No. H-6911-94

APV R3BS Positive Displacement Pump and Balance Tank Skid. Model: R3BS. S/N: H-6911-94. Pumping capacity: 17.8 gpm. Maximum capacity: 36 gpm. Maximum speed: 900 rpm. Displacement: 6.40 gpm/100 rpm. Seal option: double mechanical with flushing. Reliance S-2000 Motor, 2 hp, 1725 rpm, 208-230/460-480 V, 6.4-6.4/3.2-3.4 amps, 60 Hz, 3 phase. Dodge Master XL Speed Reducer, 6.2 ratio, torque of 835 lb-in, max. input hp 3.88, final rpm: 278. (2) 13 gal tanks with 15-1/2 in dia. top covers and two 3/4 in. dia. s-line inlets. Lightnin Portable Mixer, Model: SIU05T, S/N: 95/800000, (3) 8 in. dia. propellers. Reliance Electric Motor, 1/15 hp, 1600 rpm, 115 V, 1.1 amps, 60 Hz. Stainless steel frame mounted. (4) Wheels for easy maneuverability. Inlets: (3) 1 in. dia. tank infeeds. Outlets: (1) 1 in. dia s-line fitting. Overall dimensions: 48 in. L x 38 1/2 in. W x 69 in. H.

I/A Series Magnetic Flow Transmitter, Model: IMT20-5A16FGZ-T, supply power: 120 Vac, 30 VA max, 4-20 milliamps (current out), 50/60 Hz. Foxboro 8000A Series Magnetic Flowtube, MAWP 450 psi @ 200 °F, MAWP 150 psi @ 350 °F. Woods E-TRAC AC Inverter- 2 HP, input: 2.8 KVA, 230 V, 12.4 amps, 50/60 Hz, single phase, output (cont.): 3.0 KVA, 230 V, 7.5 amps, 3 phase, 7.5 amps.



