

Single Wall Stainless Steel 3,000 Gallon Tank with motor, transmission, and agitator. Allis Chalmers Motor information, Serial 51-460-320, 15 hp, 1,750 rpm, 208/220/440 volt, 38.6-38.6/19.3 amps, Model Flex transmission, Gear Ratio, 31.4 output 56 rpm, service 10.6 hp, 1,750 rpm. Inside dimensions 48 in. diameter x 143 in. H. Agitator paddle 28 in. L x 8 in. W, it has (4) paddles 51 in. diameter, one smaller on the bottom is 16 in. L, 4 in. W, 37 in. D. It has (8) wave stopper blades 6 in. W x 48 in. L, (5) inlets on top, (4) of them are 1-1/2 in., Bottom outlet 2 in. Overall dimensions 100 in. diameter x 20 ft. H.



