

## Single Shell Liquid Sugar Tank- 40 Gallon

Mfg:

Model:

Stock No. SGMT540.7a

Serial No.

Single Shell Liquid Sugar Tank- 40 Gallon. Stainless steel. Lesson Pump motor, 1-1/2 hp, 3450 rpm, 115 V, 17 FLA, Duty work; 60 Hz, 208/230 V, FLA 8.5. Waukesha pump, C-series, Model: C100, S/N: 331085 03, pump number: 1850. Inlet: 1-1/4 in. 'S' line. Outlet: 3/4 in. 'S' line. Agitating Mixer: Baldor motor, 1/2 hp, 1725 rpm, 115/230 V, 8/4 amps, 60 Hz, 1 phase. Shaft dimensions: 1/2 in. dia. x 28 in. L. with (3) propellers. Propeller dia.: 2-1/2 in. Bottom electric heating elements. Liquid level controller. Control panel has two sources of power, and additional (4) connections for 110 V. Stainless steel base/frame on casters. Tank outlet: 1 in. threaded female. Overall dimensions: 47 in. L x 24 in. W x 56 in. H.



