

Tranter Inc. Supercharger Plate Heat Exchanger - 513.7 Sq. Ft.

Mfg: Tranter Inc.

Model: S-3-HP-154

Stock No: SHCA1181.3a

Serial No: P-30014-H

Tranter Inc. Supercharger Plate Heat Exchanger. Model: S-3-HP-154. S/N: P-30014-H. S.O: 81343. Item no. 9039, drawing No. D-81343. Heat transfer surface area: 513.7 sq. ft. (154) 316 Stainless steel plates (0.9 mm thickness). MAWP: 100 psi. Maximum temperature: 250°F, Test Pressure 150 PSIG. Plate pack dimensions min/max: 28 in. and 72 in. Inlets: (2) 4-bolt, 2 in. dia. flange. Outlets: (2) 4-bolt, 2 in. dia. flange. Net Weight (Lbs) 2970. Overall dimensions: 8 ft. 2 in. L x 1 ft. 11 in. W x 5 ft. 6 in. H.



